



**Manufacturer:**  
ÅngströmBond®

**Product Name:**  
ÅngströmBond® AB9001MT Thixotropic Epoxy,  
Room Temperature & Heat Cure (2.5g)

**Manufacturer Part Number:**  
AB9001MT-2.5G



Learn More

▶ Click here for more details on the ÅngströmBond® AB9001MT Thixotropic Epoxy, Room Temperature & Heat Cure (2.5g)



**ÅNGSTRÖMBOND®**

Adhesives

Advanced Polymers for High Tech Applications

**ÅNGSTRÖMBOND® 9001 MT**

**Thixotropic Adhesive for MT, MTRJ and Specialty Connectors**

**Description:**

ÅNGSTRÖMBOND® 9001 MT is a two-part, room temperature curing adhesive designed specifically for use in MT and MTRJ connector assemblies. The blue color of this non-sagging thixotropic adhesive allows for easy polishing. It produces low stress during cure, thereby eliminating fiber cracking in both single and multimode connectors. ÅNGSTRÖMBOND® 9001 MT is an excellent choice sealing and encapsulating small units where a strong bond to glass, ceramic, plastics or metals are required. It offers high impact, moisture, and chemical resistance. Available in unpigmented version: AB9001MTUP.

**Typical Physical Properties:**

AB9001MT Color Mixed:	Dark blue
AB9001MTUP Color Mixed:	Clear
Specific Gravity, g/cc:	1.15
Mixed Viscosity @ 25°C, cps:	50,000-55,000
Service Temperature Range, °C:	-65 to 130
Glass Transition, °C:	
(cured 90C/15 min)	93
Hardness, Shore D:	78
Mix Ratio by Weight,	
Resin to Hardener:	100/30
Dielectric Strength:	> 400
Solids Content:	100%
Lap Shear Strength, psi:	2950

**Handling Characteristics:**

Working Life:	30-45 Minutes
Minimum Cure Schedule:	
@25°C	18 Hours
@65°C	1 Hour
@90°C	15 Minutes

Other intermediate cure schedules are possible depending upon user's application.

**Application Directions:**

Bi-pack Packages: Safely remove the divider clip from the package. Knead the package (multiple passes over the edge of a table works well) until a uniform color is achieved and the material is thoroughly mixed. Ensure all material from the corners of the bi-pack are mixed in. 25 passes over the edge of a table are recommended. Cut open end of package to dispense.

**De-airing:**

De-airing of mixing epoxy should be done to remove any entrapped air. Vacuum de-airing should be performed.

**Handling:**

To ensure better performance of the potted or encapsulated components, adequate cleaning of components should be performed to remove contamination such as dust, moisture, salt and oils that can cause poor adhesion.

**Storage:**

Two component epoxy resin systems should be stored between 65°F and 90°F. Refrigeration is not recommended. Most two-component epoxy resin systems are naturally susceptible to crystallization, especially when stored at temperatures below the recommended storage temperatures. Do not store epoxy materials near sources of heat. All materials should be kept in the original packaging to prevent foreign matter contamination and moisture entry.

ÅNGSTRÖMBOND® is a REGISTERED TRADEMARK of Fiber Optic Center, Inc., New Bedford MA, USA

Fiber Optic Center™, Inc. MAKES NO EXPRESS OR IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS OR OTHERWISE, with respect to its products. In addition, while the information herein is believed to be reliable, no warranty is expressed or implied regarding the accuracy of the data or the results to be obtained from the use thereof. All recommendations or suggestion for use are made without guarantee – inasmuch as conditions of use are beyond our control. The properties given are typical values, and are not intended for use in preparing specifications. Users should make their own test to determine the suitability of this product for their own purposes. This warranty is limited to a credit or replacement of the product only, and does not cover direct, indirect, consequential, incidental or any other type of damage resulting from the use of the product. Fiber Optic Center is not liable for any failure to observe the precautionary measures described in this SDS or for any misuse of the product.

ÅngströmBond 9001MT.doc Rev.D 12/2025

**Contact the professionals at Fiber Optic Center for a quote or to get more details.**

[focenter.com](http://focenter.com) • 508-992-6464 | (800) 473-4237 • [sales@focenter.com](mailto:sales@focenter.com)

23 Centre Street • New Bedford, MA 02740 USA

Product specifications and data are subject to change without notice. FOC last update 12/10/2025.